



# TECHNICAL INFORMATION

## BESTCAP A NEW DIMENSION IN “FAST” SUPERCAPACITORS

Scot Tripp  
AVX Ltd, Fleet, UK  
Tel: +44(0) 1252 770043 Email: [tripps@flt.avxeur.com](mailto:tripps@flt.avxeur.com)

Dr. Arieh Meitav  
ECR/AVX, Rehovot, Israel  
Tel: +972 8 940 7920 Email: [arieh@ecr.co.il](mailto:arieh@ecr.co.il)

# BESTCAP A NEW DIMENSION IN “FAST” SUPERCAPACITORS

Scot Tripp  
AVX Ltd, Fleet, UK  
Tel: +44(0) 1252 770043 Email: tripps@flt.avxneur.com

Dr. Arieh Meitav  
ECR/AVX, Rehovot, Israel  
Tel: +972 8 940 7920 Email: arieh@ecr.co.il

Supercapacitors or electrochemical caps are rapidly recognized as an excellent compromise between electronic capacitors such as ceramic, tantalum and aluminum electrolytic devices and batteries (Figure 1).





Figure 1. BestCap™ Electrochemical Cap vs. Conventional

Generally, supercapacitors have energy densities several orders of magnitude higher than electronic capacitors (Table 1) and power densities significantly superior to batteries.

There are, however, two negative characteristics associated with existing electrochemical capacitors,

CAPACITOR TYPE	CAP (mF)	VOLTAGE (V)	DIMENSIONS (mm)	ESR (mΩ)	CV/c.c. (mFV/c.c.)
Tantalum	0.47	6.3	6.0 x 7.0 x 3.5	100	20
	1.0	4.0	6.0 x 7.0 x 3.6	30	26
Electrolytic Aluminum solid capacitor organic semi-conductive electrolyte	1.5	4.0	∅10 x L20	15	3.2
	2.2	4.0	∅12.5 x L22	10	3.3
	2.2	6.3	∅16 x L25	15	2.8
Electrolytic Capacitor	4.7	6.3	∅16 x L26	100	6
	15	6.3	∅16 x L35.5	30	13
	22	6.3	∅18 x L41	20	13
	15	10	∅18 x L35.5	30	17
	330	10	∅76 x L114	10	6
BestCap™	250	8.0	52 x 50 x 4.0	50	200
	250	5.5	48 x 30 x 3.0	60	300
	500	5.5	48 x 30 x 5.0	30	400
	600	4.5	48 x 30 x 4.8	25	400
	700	3.5	48 x 30 x 4.2	20	400
	60	5.5	28 x 17 x 3.0	200	250
	120	5.5	28 x 17 x 5.0	100	300

Table 1. Performance of BestCap™ vs. Conventional Capacitor Technologies

Viz: high ESR and capacitance loss when called upon to supply very short duration pulses at high current. This paper will demonstrate how the BestCap successfully addresses both of these issues.

## EDLCs

To understand the benefits offered by the BestCap, it is necessary to examine how an electrochemical capacitor works. The most significant difference between an electronic capacitor and an electrochemical capacitor is that the charge transfer is carried out by the electrons in the former and by electrons and ions in the latter. The anions and cations involved in double layer supercapacitors are contained in the electrolyte which maybe liquid, (normally an aqueous or organic solution) or solid. The solid electrolyte is almost universally a conductive polymer.

Electrons are relatively fast moving and therefore

transfer charge “instantly”. However, ions have to move relatively slowly from anode to cathode, and hence a finite time is needed to establish the full nominal capacitance of the device. This nominal capacitance is normally measured at 1 second.

## BestCap – A New Dimension in Fast Supercapacitors

We may summarize the differences between EDLC (Electrochemical Double Layer Capacitors) and electronic capacitors as shown in Table 2 below:

<ul style="list-style-type: none"> <li>• A capacitor basically consists of two conductive plates (electrodes), separated by a layer of dielectric material.</li> </ul>
<ul style="list-style-type: none"> <li>• These dielectric materials may be ceramic, plastic film, paper, aluminum oxide, etc.</li> </ul>
<ul style="list-style-type: none"> <li>• EDLCs do not use a discrete dielectric interphase separating the electrodes.</li> </ul>
<ul style="list-style-type: none"> <li>• EDLCs utilize the charge separation, which is formed across the electrode - electrolyte interface.</li> </ul>
<ul style="list-style-type: none"> <li>• The EDLC constitutes two types of charge carriers: IONIC species on the ELECTROLYTE side and ELECTRONIC species on the ELECTRODE side.</li> </ul>

Table 2.

Because highly activated carbon is used as the electrode material, each carbon particle functions as a double layer capacitor having a capacitance value of  $C_n$  (Figure 2).




Figure 2. Simplified Equivalent Circuit of Electrochemical Capacitor

Upon charging the capacitor, the charge has to be transferred through two resistances electronic ( $R_e$ ) at the carbon electrode and at the carbon - current collector interface ( $R_c$ ), and ionic ( $R_i$ ) passing through the electrolyte. Therefore, the equivalent circuit of the EDLC is given by the above R-C combination, where  $R_1$ ,  $R_2$  and  $R_n$  are the internal resistances of the activated carbons.

Since the EDL capacitor is comprised of capacitors having various resistances, the charge/discharge voltage and charge/discharge time will define the apparent available capacity. Charging or discharging at a high rate may result in an apparently smaller capacitance than when done at a lower rate. This is due to the small capacitors that have large internal resistance not being fully charged or discharged which results in a large voltage drop at the start of measurement.

## BestCap Pulse Performance

BestCap technology is based on a patented, highly conductive polymeric, proton conductive electrolyte. The innovation of BestCap is that this polymer electrolyte possesses very high ionic conductivity, thereby providing low ESR in the range of 20-200 milliohms and maintaining high apparent capacitance for very short pulses.

## BestCap – A New Dimension in Fast Supercapacitors

These two factors are critical in determining the total voltage drop in short pulse operations, such as in GSM and other pulsed-mode digital mobile phones. Figure 3 shows the voltage time relationship for a capacitor. First there is the instantaneous voltage drop  $\Delta V(1R)$  caused by the ESR, followed by  $\Delta V(Q)$ , which is a function of the available capacitance.




Figure 3. Voltage-Time Relation of Cap Unit

$$C = I\Delta t(V_0 - V_t - IR) \rightarrow I = C \cdot (V_0 - V_t) / (R \cdot C + t)$$

$$\text{Spec. Power} = I \cdot (V_0 - I \cdot R + V_t) / 2 \text{ per unit Volume}$$

$$\text{Spec. Energy} = I \cdot \Delta t \cdot (V_0 - I \cdot R + V_t) / 2 \text{ per unit Volume}$$

$$R = \text{ESR}$$

Now consider the available capacitance for very short pulse widths and for various EDLCs from a number of manufacturers, as shown in Figure 4. It can be clearly seen that virtually all EDLCs with the exception of BestCap lose >>90% of their nominal capacitance when used in the millisecond range.




Figure 4. Actual Capacitance vs. Pulse Width

This combined with their higher ESF, means that they will exhibit very high significant voltage drop under short pulse conditions, whereas the voltage drop for BestCap is very small.

When used in a mobile phone, for example, and placed between the battery and the power amplifier, BestCap reduces the pulsed current drain on the battery thereby significantly increasing “Talk Time” from the battery.

## Other BestCap Characteristics

The material systems used in the BestCap structure features the following characteristics:

- Totally solid state, no liquids or gels used.
- Completely non-toxic.
- Capable of very thin formats with thickness down to < 0.7mm.
- Shock resistance to > 30000G's.
- Easy to produce in various voltage ratings.
- Non-Polar.
- Low leakage current - < 0.05 $\mu$ A/mF.
- Capacitance values 40-500mF.

## Summary

The high conductivity proton polymer electrolyte utilized in BestCap allows high current, short duration pulses to be delivered with minimal voltage drop. The product uses only “green” material and is physically very robust.




Figure 5. Discharge of a 500 mAh Li-ion Battery (48 x 30 x 6.3) at a GSM “talk” Simulation Mode

## USA

**AVX Myrtle Beach, SC  
Corporate Offices**  
Tel: 843-448-9411  
FAX: 843-626-5292

**AVX Northwest, WA**  
Tel: 360-699-8746  
FAX: 360-699-8751

**AVX North Central, IN**  
Tel: 317-848-7153  
FAX: 317-844-9314

**AVX Mid/Pacific, MN**  
Tel: 952-974-9155  
FAX: 952-974-9179

**AVX Southwest, AZ**  
Tel: 480-539-1496  
FAX: 480-539-1501

**AVX South Central, TX**  
Tel: 972-669-1223  
FAX: 972-669-2090

**AVX Southeast, NC**  
Tel: 919-878-6223  
FAX: 919-878-6462

**AVX Canada**  
Tel: 905-564-8959  
FAX: 905-564-9728

## EUROPE

**AVX Limited, England  
European Headquarters**  
Tel: ++44 (0) 1252 770000  
FAX: ++44 (0) 1252 770001

**AVX S.A., France**  
Tel: ++33 (1) 69.18.46.00  
FAX: ++33 (1) 69.28.73.87

**AVX GmbH, Germany - AVX**  
Tel: ++49 (0) 8131 9004-0  
FAX: ++49 (0) 8131 9004-44

**AVX GmbH, Germany - Elco**  
Tel: ++49 (0) 2741 2990  
FAX: ++49 (0) 2741 299133

**AVX srl, Italy**  
Tel: ++390 (0)2 614571  
FAX: ++390 (0)2 614 2576

**AVX Czech Republic, s.r.o.**  
Tel: ++420 (0)467 558340  
FAX: ++420 (0)467 558345

## ASIA-PACIFIC

**AVX/Kyocera, Singapore  
Asia-Pacific Headquarters**  
Tel: (65) 258-2833  
FAX: (65) 350-4880

**AVX/Kyocera, Hong Kong**  
Tel: (852) 2-363-3303  
FAX: (852) 2-765-8185

**AVX/Kyocera, Korea**  
Tel: (82) 2-785-6504  
FAX: (82) 2-784-5411

**AVX/Kyocera, Taiwan**  
Tel: (886) 2-2696-4636  
FAX: (886) 2-2696-4237

**AVX/Kyocera, China**  
Tel: (86) 21-6249-0314-16  
FAX: (86) 21-6249-0313

**AVX/Kyocera, Malaysia**  
Tel: (60) 4-228-1190  
FAX: (60) 4-228-1196

**Elco, Japan**  
Tel: 045-943-2906/7  
FAX: 045-943-2910

**Kyocera, Japan - AVX**  
Tel: (81) 75-604-3426  
FAX: (81) 75-604-3425

**Kyocera, Japan - KDP**  
Tel: (81) 75-604-3424  
FAX: (81) 75-604-3425

### Contact:

NOTICE: Specifications are subject to change without notice. Contact your nearest AVX Sales Office for the latest specifications. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements or suggestions concerning possible use of our products are made without representation or warranty that any such use is free of patent infringement and are not recommendations to infringe any patent. The user should not assume that all safety measures are indicated or that other measures may not be required. Specifications are typical and may not apply to all applications.

© AVX Corporation



<http://www.avxcorp.com>

S-BC00M301-N